

PrimaVision Mini (20W, 35W & 50W) for CDM – Miniature size to enhance creativity

PrimaVision Mini for CDM

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Benefits

- Miniaturization enables stylish luminaire design and retrofit halogen replacement
- Optimal lamp performance thanks to minimal lamp power tolerance
- Easy luminaire design-in

Features


- Loop Through feature (in independent version)
- Smallest gear and highest wattage in miniature size
- Minimal lamp power spread
- Microprocessor-controlled
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application


- 20/35/50 W accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Mini for CDM

Versions



Dimensional drawing



| Product | D1 | C1 | A1 | A2 | A3 | B1 |
|--|--------|---------|----------|----------|----------|---------|
| HID-PV m 20 /I CDM 220-240V 50/60Hz | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |
| HID-PV m 35/I CDM 220-240V 50/60Hz | 4.8 mm | 34.0 mm | 234.7 mm | 225.1 mm | 202.0 mm | 49.4 mm |

| Product | D1 | C1 | A1 | A2 | B1 |
|--|--------|---------|---------|---------|---------|
| HID-PV m 20 /S CDM 220-240V 50/60Hz | 4.2 mm | 30.2 mm | 97.3 mm | 88.3 mm | 43.3 mm |

| Operating and Electrical | |
|--------------------------|--------------|
| Input frequency | 50 to 60 Hz |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |

Operating and Electrical

| Order Code | Full Product Name | Number of products on MCB (16 A type B) (nom.) |
|------------|---|---|
| 89060000 | HID-PV m 20 /I CDM HPF 220-240V 50/60Hz | 24 |
| 89164500 | HID-PV m 35 /I CDM 220-240V 50/60Hz | 24 |

| Order Code | Full Product Name | Number of products on MCB (16 A type B) (nom.) |
|------------|-------------------------------------|---|
| 67159600 | HID-PV m 20 /S CDM 220-240V 50/60Hz | 32 |

Mechanical and Housing

PrimaVision Mini for CDM

| Order Code | Full Product Name | Housing |
|------------|---|-------------|
| 89060000 | HID-PV m 20 /I CDM HPF 220-240V 50/60Hz | Independent |
| 89164500 | HID-PV m 35 /I CDM 220-240V 50/60Hz | Independent |

| Order Code | Full Product Name | Housing |
|------------|-------------------------------------|---------|
| 67159600 | HID-PV m 20 /S CDM 220-240V 50/60Hz | /S |

