

PrimaVision Mini (20W, 35W & 50W) for CDM – Miniature size to enhance creativity

PrimaVision Mini for CDM

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Benefits

- Miniaturization enables stylish luminaire design and retrofit halogen replacement
- Optimal lamp performance thanks to minimal lamp power tolerance
- Easy luminaire design-in

Features


- Loop Through feature (in independent version)
- Smallest gear and highest wattage in miniature size
- Minimal lamp power spread
- Microprocessor-controlled
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application



- 20/35/50 W accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Mini for CDM

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m 35 /S CDM 220-240V 50/60Hz	4.2 mm	30.2 mm	97.3 mm	88.3 mm	43.3 mm
HID-PV m 50 /S CDM HPF 220-240V 50/60Hz	4.2 mm	30.2 mm	97.3 mm	88.3 mm	43.3 mm
HID-PV m 20 /S CDM 220-240V 50/60Hz	4.2 mm	30.2 mm	97.3 mm	88.3 mm	43.3 mm

Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20/S CDM HPF 220-240V	4.2 mm	30.0 mm	97.3 mm	88.3 mm	43.3 mm

Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V

General Information

Number Of Lamps	1 piece/unit
Lamp Type	CDM

General Information

PrimaVision Mini for CDM

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700656766	HID-PV m PGJ5 20/S CDM HPF 220-240V	24
913700665966	HID-PV m 50 /S CDM HPF 220-240V 50/60Hz	24

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700696066	HID-PV m 20 /S CDM 220-240V 50/60Hz	32
913700696166	HID-PV m 35 /S CDM 220-240V 50/60Hz	24

Mechanical and Housing

Order Code	Full Product Name	Housing
913700656766	HID-PV m PGJ5 20/S CDM HPF 220-240V	Standard
913700665966	HID-PV m 50 /S CDM HPF 220-240V 50/60Hz	/S

Order Code	Full Product Name	Housing
913700696066	HID-PV m 20 /S CDM 220-240V 50/60Hz	/S
913700696166	HID-PV m 35 /S CDM 220-240V 50/60Hz	/S

System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700656766	HID-PV m PGJ5 20/S CDM HPF 220-240V	20 W
913700665966	HID-PV m 50 /S CDM HPF 220-240V 50/60Hz	50 W

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700696066	HID-PV m 20 /S CDM 220-240V 50/60Hz	20 W
913700696166	HID-PV m 35 /S CDM 220-240V 50/60Hz	39 W

