



PrimaVision Economy (35, 50 and 70 W) for CDM – The cost- effective solution

PrimaVision Economy for CDM lamps

Single CDM lamp operation, single HID electronic gear – improves cost effectiveness and increases luminaire design flexibility

优点

- Cost-effective, plus design flexibility
- Optimal lamp performance thanks to minimal lamp power tolerance
- Lamp life increased by up to 30% for CDM lamps

特点

- Minimal lamp power spread
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Lifetime of 30,000 hours

应用

- 35, 50 and 70 W: accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only
- Available in standard (S) and independent (I) versions