

High quality and robust performance

PrimaVision Compact for CDM

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- CDM lamp life increased by up to 30%
- Eliminates all visible lamp flicker

Features

- Minimal lamp power spread
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application



- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Compact for CDM

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV C 35 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm
HID-PV C 70 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V

General Information

Number Of Lamps	1 piece/unit
Lamp Type	CDM

Mechanical and Housing

Housing	/I
---------	----

General Information

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700653166	HID-PV C 35 /I CDM 220-240V 50/60Hz NG	24

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700653266	HID-PV C 70 /I CDM 220-240V 50/60Hz NG	20

System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700653166	HID-PV C 35 /I CDM 220-240V 50/60Hz NG	35 W

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700653266	HID-PV C 70 /I CDM 220-240V 50/60Hz NG	70 W

PrimaVision Compact for CDM

