

# High quality and robust performance

## PrimaVision Compact for CDM

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

### Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- CDM lamp life increased by up to 30%
- Eliminates all visible lamp flicker

### Features

- Minimal lamp power spread
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

### Application


- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

# PrimaVision Compact for CDM

## Versions



## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV C 70 /S CDM	4.9 mm	32.2	109.6	98.5	74.4	63.7
220-240V 50/60Hz NG		mm	mm	mm	mm	mm
HID-PV C 35 /S CDM	4.9 mm	32.2	109.6	98.5	74.4	63.7
220-240V 50/60Hz NG		mm	mm	mm	mm	mm

### Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V

### General Information

Number Of Lamps	1 piece/unit
Lamp Type	CDM

### Mechanical and Housing

Housing	/S
---------	----

## General Information

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700652766	HID-PV C 35 /S CDM 220-240V 50/60Hz NG	24

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913700652966	HID-PV C 70 /S CDM 220-240V 50/60Hz NG	20

## System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700652766	HID-PV C 35 /S CDM 220-240V 50/60Hz NG	35 W

Order Code	Full Product Name	Rated Ballast-Lamp Power
913700652966	HID-PV C 70 /S CDM 220-240V 50/60Hz NG	70 W

## PrimaVision Compact for CDM

