

# PrimaVision Power (100W & 150W) for CDM – High power packed in a small size

## PrimaVision Power for CDM

PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

### 优点

- Optimal lamp performance thanks to minimal lamp power tolerance
- Lamp life increased by up to 30% for CDM lamps
- Eliminates all visible lamp flicker

### 特点

- Loop Through feature (in independent version)
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

### 应用


- 100 and 150 W: high-bay area, accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

# PrimaVision Power for CDM

## Versions



## 二维绘图



Product	D1	C1	A1	A2	B1	B2
HID-PV C 150 /S CDM	4.8 mm	32.0	135.0	123.5	75.0	63.5
220-240V 50/60Hz		mm	mm	mm	mm	mm

