

PrimaVision Power (100W & 150W) for CDM – High power packed in a small size

PrimaVision Power for CDM

PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

Benefits

- Optimal lamp performance thanks to minimal lamp power tolerance
- Lamp life increased by up to 30% for CDM lamps
- Eliminates all visible lamp flicker

Features


- Loop Through feature (in independent version)
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application


- 100 and 150 W: high-bay area, accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

PrimaVision Power for CDM

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV C 150 /S CDM	4.8 mm	32.0	135.0	123.5	75.0	63.5
220-240V 50/60Hz		mm	mm	mm	mm	mm

Product	D1	C1	A1	A2	B1
HID-PV C 150 /I CDM	4.8 mm	34.2 mm	223.9 mm	206.0 mm	82.7 mm
220-240V 50/60Hz					

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
General Information	
Number Of Products On MCB (16A Type B) (Nom)	6
Number Of Lamps	1 piece/unit
Lamp Type	CDM
System characteristics	
Rated Ballast-Lamp Power	150 W

PrimaVision Power for CDM

Mechanical and Housing

Order Code	Full Product Name	Housing	Order Code	Full Product Name	Housing
913700614066	HID-PV C 150 /S CDM 220-240V 50/60Hz	/S	913700624466	HID-PV C 150 /I CDM 220-240V 50/60Hz	/I

