



# Incredible colors, amazing atmosphere

## **MASTER SDW-T**

Range of high-efficiency, discharge lamps with warm color to be used in open luminairs

#### **Benefits**

- Exceptional brightness and color rendering especially of warm colors, e.g. red and gold
- $\boldsymbol{\cdot}$  High lamp efficacy results in low operating costs and low heat generation
- $\cdot$  Long lamp life compared with incandescent and halogen lamps

#### **Features**

- · Unique warm color quality
- Lamp design is well-suited to be used in luminairs for power-spots (high intensity) and high-bay general lighting

#### **Application**

• Shop lighting (create cosy atmosphere e.g. in furniture shops), excellent display of fresh goods (at butchers, bakeries, flower-shops) and decorative outdoor lighting (gas-lantern imitation)

### **Warnings and Safety**

- · Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions








LPPR SDW-T 100W PG12-1

# Dimensional drawing



Product	D (max)	0	L	C (max)
MASTER SDW-T 100W/825 PG12-1 1SL/12	32 mm	18.3 mm	91 mm	149 mm
MASTER SDW-T 35W/825 PG12-1 1SL/12	32 mm	12.7 mm	91 mm	149 mm
MASTER SDW-T 50W/825 PG12-1 1SL/12	32 mm	15.4 mm	91 mm	149 mm

General Information	
Cap-Base	PG12-1
Operating Position	UNIVERSAL
Light Technical	
Chromaticity Coordinate X (Nom)	0.478
Chromaticity Coordinate Y (Nom)	0.415
Color Designation	Golden White
Correlated Color Temperature (Nom)	2500 K
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T31

# Light Technical

		Color rendering	Luminous Efficacy	
Order Code	Full Product Name	index (CRI)	(rated) (Nom)	Luminous Flux
73403715	MASTER SDW-T 50W/825 PG12-1	82	45.45 lm/W	2,500 lm
	1SL/12			
73404415	MASTER SDW-T 100W/825 PG12-1	83	52.58 lm/W	5,100 lm
	1SL/12			
73402015	MASTER SDW-T 35W/825 PG12-1	81	40 lm/W	1,320 lm
	1SL/12			

## Operating and Electrical

1			
Order Code	Full Product Name	Voltage (Nom)	Power Consumption
73403715	MASTER SDW-T 50W/825 PG12-1	90 V	55.5 W
	1SL/12		
73404415	MASTER SDW-T 100W/825 PG12-1	97 V	97.0 W
	1SL/12		

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
73402015	MASTER SDW-T 35W/825 PG12-1	98 V	33.3 W
	1SL/12		

## **MASTER SDW-T**


#### Mechanical and Housing

Order Code	Full Product Name	Bulb Material	
73403715	MASTER SDW-T 50W/825 PG12-1 1SL/12	Soft Glass	
73404415	MASTER SDW-T 100W/825 PG12-1 1SL/12	Hard Glass	

Order Code	Full Product Name	Bulb Material
73402015	MASTER SDW-T 35W/825 PG12-1 1SL/12	Soft Glass

#### **Approval and Application**

		Energy	Mercury (Hg)	Mercury (Hg)
		Consumption	Content	Content
Order Code	Full Product Name	kWh/1000 h	(Max)	(Nom)
73403715	MASTER SDW-T	56 kWh	7.6 mg	7.6 mg
	50W/825 PG12-1 1SL/12			
73404415	MASTER SDW-T	97 kWh	11.4 mg	11.4 mg
	100W/825 PG12-1			
	1SL/12			
73402015	MASTER SDW-T	34 kWh	3.8 mg	3.8 mg
	35W/825 PG12-1 1SL/12			





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.