



Product Description

MASTER SDW-T

Range of high-efficiency, discharge lamps with warm colour to be used in open luminaires

Benefits

- Exceptional brightness and colour rendering especially of warm colours, e.g. red and gold
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps

Features

- Warm white colour impression, very good colour rendering, especially superb red rendition
- Lamp design is well-suited to be used in luminaires for power-spots (high intensity) and high-bay general lighting

Application

- Shop lighting (create cosy atmosphere e.g. in furniture shops), excellent display of fresh goods (at butchers, bakeries, flower-shops) and decorative outdoor lighting (gas-lantern imitation)

Warnings and Safety

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


MASTER SDW-T

Versions



LPPR SDW-T 100W PG12-1

Dimensional drawing



Product	D (max)	O	L	C (max)
MASTER SDW-T 100W/825 PG12-1 1SL/12	32 mm	18.3 mm	91 mm	149 mm

