



Product Description

MASTER SDW-T

Range of high-efficiency, discharge lamps with warm colour to be used in open luminaires

Benefits

- Exceptional brightness and colour rendering especially of warm colours, e.g. red and gold
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps

Features

- Warm white colour impression, very good colour rendering, especially superb red rendition
- Lamp design is well-suited to be used in luminaires for power-spots (high intensity) and high-bay general lighting

Application


- Shop lighting (create cosy atmosphere e.g. in furniture shops), excellent display of fresh goods (at butchers, bakeries, flower-shops) and decorative outdoor lighting (gas-lantern imitation)

MASTER SDW-T

Versions



Dimensional drawing



Product	D (max)	O	L	C (max)
MASTER SDW-T 100W/825 PG12-1 1SL/12	32 mm	18.3 mm	91 mm	149 mm

Colour Rendering Diagrams

