



产品描述

MASTER SDW-TG 小型

系列高光效放电灯,用于 MASTERColour CDM-T 光源的小型开放式灯具

优点

- 还生鲜水果鲜艳的颜色,提高顾客的购买欲望
- 优异的红黄色还原能力,特别适合照射红色物体,如番茄,橘子,肉类,面包,皮具,红木家具等
- 卓越的颜色稳定性和一致性,提升和维护商铺的整体形象
- 舒适温馨的家庭氛围,给您的客户宾至如归的感觉:色温 2500K
- 更自由的商铺灯光设计
- 任意燃点位置,更自由的灯光设计
- CDM-T 同样尺寸(不同灯头,防止系统安装错误),可用于同一款式灯具,保持店铺形象的一致性
- 保护被照物体:UV 防护
- 节能省电
- 高光效:2 倍于卤钨灯
- 长寿命:6 倍于卤钨灯,大大节省灯管替换成本
- 热量低:比卤钨灯减少 30%

特点

- 暖白光,良好的显色性,对红色表现更出众
- 设计的光源适用于 MASTERColour CDM-T 光源的灯具
- 防紫外线玻壳可减少商品褪色的危险

应用


- 商业照明,环境照明,重点照明
- 超市生鲜水果区,皮具店,面包店,肉店,水果店,家具店
- 室内公共场所需营造家庭氛围的照明

安全提示

- Use only with dedicated Philips control gear
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER SDW-TG 小型

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTER SDW-TG Mini 100W/825	20 mm	0.75 in	18 mm	54.5 mm	57.5 mm	56 mm	110 mm
GX12-1 1CT/12							
MASTER SDW-TG Mini 50W/825	20 mm	0.75 in	14.5 mm	53.5 mm	56.5 mm	55 mm	103 mm
GX12-1 1CT/12							

控制调光	
可调光	否
基本信息	
底座	GX12-1
50% 故障条件下的使用寿命 (标称)	10000 h
操作位置	UNIVERSAL
系统说明	na
照明科技	
色度坐标 X (标称)	0.478
色度坐标 Y (标称)	0.415
颜色代码	825
颜色名称	金色 白色
相关色温 (标称)	2500 K
显色指数 (最小)	80
10000 小时下的光通维持率 (最低)	65 %
10000 小时下的光通维持率 (标称)	75 %
2000 小时下的光通维持率 (最低)	85 %
2000 小时下的光通维持率 (标称)	95 %
5000 小时下的光通维持率 (最低)	75 %
机械和壳体	
灯泡外观	透明
灯泡材料	玻璃
灯泡外形	T19

应用

Order Code	Full Product Name	能耗 kWh/1000 h	汞 (Hg) 含量(最高)	汞 (Hg) 含量(标称)
928158905131	MASTER SDW-TG Mini 100W/825	102 kWh	15.2 mg	15.2 mg
	GX12-1 1CT/12			
928159905131	MASTER SDW-TG Mini 50W/825	54 kWh	5.7 mg	5.7 mg
	GX12-1 1CT/12			

运营和电气 (1/2)

Order Code	Full Product Name	电压 (最高)	电压 (最低)	电压 (标称)	功率(标称值)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	98 V	84 V	91 V	102.0 W

Order Code	Full Product Name	电压 (最高)	电压 (最低)	电压 (标称)	功率(标称值)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	90 V	78 V	85 V	54.0 W

运营和电气 (2/2)

Order Code	Full Product Name	重新点火时间 (分钟)(最大)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	1.5 min

MASTER SDW-TG 小型

Order Code	Full Product Name	重新点火时间 (分钟)(最大)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1	1.0 min
	1CT/12	

基本信息

Order Code	Full Product Name	20% 故障条件下的使用寿命 (标称)	5% 故障条件下的使用寿命 (标称)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	8000 h	5000 h

Order Code	Full Product Name	20% 故障条件下的使用寿命 (标称)	5% 故障条件下的使用寿命 (标称)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	9000 h	7000 h

灯具设计要求

Order Code	Full Product Name	灯泡温度 (最高)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	650 °C

Order Code	Full Product Name	灯泡温度 (最高)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	500 °C

照明科技 (1/2)

Order Code	Full Product Name	显色指数 (标称)	5000 小时下的光通维持率 (标称)	光效(额定) (标称)	光通量 (标称)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	82	80 %	52 lm/W	5300 lm

Order Code	Full Product Name	显色指数 (标称)	5000 小时下的光通维持率 (标称)	光效(额定) (标称)	光通量 (标称)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	81	85 %	44 lm/W	2400 lm

照明科技 (2/2)

Order Code	Full Product Name	光通量 (额定)(最小)	光通量 (额定)(标称)
928158905131	MASTER SDW-TG Mini 100W/825 GX12-1 1CT/12	4400 lm	5300 lm

Order Code	Full Product Name	光通量 (额定)(最小)	光通量 (额定)(标称)
928159905131	MASTER SDW-TG Mini 50W/825 GX12-1 1CT/12	2100 lm	2400 lm

