



Product Description

SOX

Low Pressure Sodium lamp

Benefits

- High luminous efficacy leads to low energy consumption


Features

- Uniform sodium distribution in the discharge tube by means of dimples for a more stable discharge, higher efficacy and better lumen maintenance and lamp life
- Monochromatic yellow colour with non-existent colour rendering

Application

- Road lighting, railway marshalling yards and crossings, airports, harbours and docks, quarries, foundries and rolling mills
- Security and orientation lighting

Dimensional drawing



Product	D (max)	C (max)
SOX 90W BY22d 1SL/12	66 mm	528 mm
SOX 35W BY22d 1SL/12	52 mm	311 mm
SOX 180W BY22d 1SL/6	66 mm	1120 mm
SOX 180W BY22d T65 1SL	66 mm	1120 mm
SOX 55W BY22d 1SL/12	52 mm	425 mm
SOX 135W BY22d 1SL/12	66 mm	775 mm