



Lamp Description

Circline

T9 4-Pin Circular Fluorescent Lamps.

Versions





G10q, T9



G10q, C-T9

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
FC12T9/COOL WHITE PLUS	31.0 mm	26.2 mm	292.1 mm	304.8 mm	239.5 mm	246.1 mm
FC8T9/DAYDLX/22W/8 12PK	31.0 mm	26.2 mm	203.2 mm	215.9 mm	149.1 mm	155.7 mm
FC12T9/DAYLIGHT DELUXE 12PK	31.0 mm	26.2 mm	292.1 mm	304.8 mm	239.5 mm	246.1 mm
FC8T9/COOL WHITE PLUS	31.0 mm	26.2 mm	203.2 mm	215.9 mm	149.1 mm	155.7 mm
FC16T9/COOL WHITE PLUS	30.9 mm	27.1 mm	393.7 mm	406.4 mm	341.0 mm	347.7 mm

Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
FC8T9/SOFT WHITE/22W/8 12 PK	31.0 mm	26.2 mm	203.2 mm	215.9 mm	149.1 mm	155.7 mm
FC12T9/SOFTWHITE/32W/1 2 12PK	31.0 mm	26.2 mm	292.1 mm	304.8 mm	239.5 mm	246.1 mm

Controls and Dimming	
Dimmable	No
General Information	
Cap-Base	G10Q
Life To 50% Failures (Nom)	13000 h
Mechanical and Housing	
Bulb Shape	C-T9

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
391169	FC8T9/COOL WHITE PLUS	8.0 mg
392357	FC8T9/DAYDLX/22W/8 12PK	8.0 mg
391177	FC12T9/COOL WHITE PLUS	8.0 mg
262600	FC12T9/DAYLIGHT DELUXE 12PK	8.0 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
391185	FC16T9/COOL WHITE PLUS	8.0 mg
392225	FC8T9/SOFT WHITE/22W/8 12 PK	8.0 mg
391227	FC12T9/SOFTWHITE/32W/12 12PK	-

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Rated) (Nom)
391169	FC8T9/COOL WHITE PLUS	0.37 A	61 V	20.5 W
392357	FC8T9/DAYDLX/22W/8 12PK	0.37 A	61 V	20.5 W
391177	FC12T9/COOL WHITE PLUS	0.43 A	84 V	31 W
262600	FC12T9/DAYLIGHT DELUXE 12PK	0.43 A	84 V	31 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Rated) (Nom)
391185	FC16T9/COOL WHITE PLUS	0.42 A	109 V	39.5 W
392225	FC8T9/SOFT WHITE/22W/8 12 PK	0.37 A	61 V	20.5 W
391227	FC12T9/SOFTWHITE/32W/12 12PK	0.43 A	84 V	31 W

Light Technical

Order Code	Full Product Name	Color		Correlated Color Temperature (Nom)	Color Rendering			Luminous Flux (Nom)
		Code	Color Designation		Index (Nom)	Lumen Maintenance 2000 h (Nom)	Lumen Maintenance 5000 h (Nom)	
391169	FC8T9/COOL WHITE PLUS	33	Cool White (CW)	4100 K	62	80 %	71 %	1050 lm
392357	FC8T9/DAYDLX/22W/8 12PK	54	Cool Daylight	6200 K	79	80 %	71 %	910 lm
391177	FC12T9/COOL WHITE PLUS	33	Cool White (CW)	4100 K	62	83 %	74 %	1800 lm
262600	FC12T9/DAYLIGHT DELUXE 12PK	54	Cool Daylight	6200 K	79	83 %	74 %	1570 lm
391185	FC16T9/COOL WHITE PLUS	33	Cool White (CW)	4100 K	62	87 %	78 %	2500 lm
392225	FC8T9/SOFT WHITE/22W/8 12 PK	830	Soft White	3000 K	80	80 %	72 %	1150 lm
391227	FC12T9/SOFTWHITE/32W/12 12PK	830	Warm White (WW)	3000 K	85	84 %	77 %	1900 lm

