



# Bright light in a small package

## T5 Retail Sales

Available in a variety of lengths and lumen packages, these T5 lamps are an ideal solution for use in compact fixtures.

### Benefits

- Lasts up to 3 years based on average usage of 2000 hours per year

### Features

- Available in a soft white color to blend in with conventional incandescent lamps or a cool white color to match fluorescent products
- Good color rendering for soft white products

### Application

- Ideal for appliances and fixtures requiring short, low-wattage lamps

### Warnings and Safety

- CAUTION: When changing lamps, turn off power to the fixture to avoid electric shock.
- Fluorescent lamps can shatter if broken.
- Handle with care and store in a safe place.


T5 Retail Sales

Versions



LPPR TL5-HE8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F28T5/TL835 ALTO UPC 15/1	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

