



Environmentally Responsible Lamps

Preheat T8

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Benefits

- Sustainable lighting solution - Reduces the impact on the environment.
- Warranty Period: 12 months.

Features

- Requires a starter or preheat switch. Several seconds of warm-up time is required before starting.
- Available in 15 watts Daylight, Warm White, Cool White, Plant Light. 30 watts Daylight and Cool White.

Application

- Ideal for under cabinet replacement lighting.

Preheat T8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/CW 25PK	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
F15T8/D 25PK	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

General Information	
Cap-Base	G13
Operating and Electrical	
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Power Consumption	15 W
Wattage Equivalent	15 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

Light Technical

Full Product		Correlated Color		Color rendering	
Order Code	Name	Color Designation	Temperature (Nom)	index (CRI)	Luminous Flux
928022803325	F15T8/CW 25PK	Cool White (CW)	4100 K	63	830 lm
928022805425	F15T8/D 25PK	Cool Daylight	6200 K	75	725 lm

