




Retail Sales T8

Retail Sales T8

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8 BRIGHT WHITE/18 ALTO SL6	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
F15T8/COOL WHITE PLUS/18 ALTO SL 6	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Retail Sales T8

General Information	
Cap-Base	G13
Operating and Electrical	
Lamp Current (Nom)	0.335 A
Voltage (Nom)	55 V
Power Consumption	15 W
Wattage Equivalent	15 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

Light Technical

Order Code	Full Product Name	Color	Correlated Color	Color	Luminous Flux
		Designation	Temperature (Nom)	rendering index (CRI)	
928022803328	F15T8/COOL WHITE PLUS/18 ALTO SL 6	Cool White (CW)	4100 K	63	830 lm
928022883028	F15T8 BRIGHT WHITE/18 ALTO SL6	Soft White	3000 K	83	990 lm

