



# Latina – simple and effective

## Latina FBH024

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. Square and round models are available. Latina comes in ready-to-install kit versions, including lamps and pre-connected separate gearbox. The round models are available in glass versions (frosted glass or clear decorative glass) or in open versions. For the open versions, the same glass designs are available as accessories (to be ordered separately). The square versions are always with glass.

### Benefits

- Easy to install and connect: all-in-one kit

### Features

- Square and round models
- Frosted or clear decorative glass

### Application

- Shops
- Offices

### Specifications

Type	FBH024
Light source	Compact fluorescent: <ul style="list-style-type: none"><li>- 2 x MASTER PL-C 2 Pin / G24d-2 / 18 W</li><li>- 2 x MASTER PL-C 2 Pin / G24d-3 / 26 W</li><li>- 2 x MASTER PL-C 4 Pin / G24q-2 / 18 W</li><li>- 2 x MASTER PL-C 4 Pin / G24q-3 / 26 W</li></ul>
Lamp included	Yes (K or lamp color 830 or 840)
Lamp position	Horizontal


Gear	Electro magnetic (low loss), 230 or 240 V / 50 Hz: <ul style="list-style-type: none"><li>- Inductive (I)</li><li>- Inductive, parallel compensated (IC)</li></ul> Electronic, 220 - 240 V / 50 - 60 Hz: <ul style="list-style-type: none"><li>- High Frequency (HF)</li></ul>
Material	Body and gear box: metal Reflector: high-gloss anodized metal
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access or after removing the front glass

Accessory (for open versions)	Frosted glass cover, clear decorative glass cover
-------------------------------	---

Accessories



Ordercode 910930025218



Ordercode 910930025318

