



FBH/S056

FBH056

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Features

- Adjustable swing out metal clip integrates easily various ceiling systems.
- Maintenance is simplified with direct lamp access from below
- Front Glass version is available

Application

- Offices
- Retail
- Hospitality

Versions



Approval and Application

Ingress protection code IP20

General Information

Compensation circuit Inductive

Gear CONV

Lamp family code PL-C/2P

Number of light sources 1 pc

Mechanical and Housing

Color White

General Information

Order Code	Full Product Name	Optical cover/lens type	Lamp power
911401153780	FBH056 1xPL-C/2P10W I WH	-	10 W
911401154080	FBS056 1xPL-C/2P10W I WH	-	10 W

Order Code	Full Product Name	Optical cover/lens type	Lamp power
911401154180	FBS056 1xPL-C/2P13W I WH	-	13 W
911401154680	FBH056 1xPL-C/2P10W I FG WH	Flat glass	10 W

