



FBH/S057

FBH057

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Features

- Adjustable swing out metal clip integrates easily various ceiling systems
- Maintenance is simplified with direct lamp access from below
- Front Glass version is available

Application

- Offices
- Retail
- Hospitality

Versions



Approval and Application

Ingress protection code	IP20
-------------------------	------

General Information

Compensation circuit	Inductive
----------------------	-----------

Gear	CONV
------	------

Lamp family code	PL-C/2P
------------------	---------

Number of light sources	1 pc
-------------------------	------

Mechanical and Housing

Color	White
-------	-------

General Information

Order Code	Full Product Name	Optical cover/lens type	Lamp power
911401153880	FBH057 1xPL-C/2P13W I FG WH	Flat glass	13 W
911401153980	FBH057 1xPL-C/2P18W I FG WH	Flat glass	18 W
911401154280	FBH057 1xPL-C/2P13W I WH	-	13 W

Order Code	Full Product Name	Optical cover/lens type	Lamp power
911401154380	FBH057 1xPL-C/2P18W I WH	-	18 W
911401154580	FBS057 1xPL-C/2P18W I WH	-	18 W

