



FBH/S058

FBH/FBS058

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Features

- Adjustable swing out metal clip integrates easily various ceiling systems.
- Maintenance is simplified with direct lamp access from below
- Front Glass version is available

Application

- Offices
- Retail
- Hospitality

Dimensional drawing

FBH/FBS058