



Smart CFL-I downlight FBS111/112/113/115/116 – a reliable way to create outstanding lighting

Theta FBS110

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

Benefits

- Safe
- Durable
- Flexible

Features

- Specular diamond faceted reflector for a wide and efficient beam
- Special sandblasted louver for glare-free visual comfort
- New class I three-way connector and sleeving to prevent electrical shocks
- New self-adjusting mounting clips for easy installation
- Suitable for wide range of retrofit energy saving lamps - 3W to 23W CFLs (may vary for different type of luminaires)
- CCC-certified; truly safe and reliable
- Available in five sizes for different cut-outs; two models can be adjusted to accommodate more types of lamp
- Elegant design; integrates perfectly into shop and hotel environments

Theta FBS110

Application

- Households
- Condominiums
- Shops
- Hotels
- Restaurants
- Offices
- Hospitals
- Shopping areas
- Office lobbies
- Hotels, restaurants, hospitals and other public areas

Specifications

| | |
|---------------------|-----------------------------------|
| Type | FBS111 (cut out Ø 125 mm version) |
| | FBS112 (cut out Ø 70 mm version) |
| | FBS113 (cut out Ø 105 mm version) |
| | FBS115 (cut out Ø 160 mm version) |
| | FBS116 (cut out Ø 175 mm version) |
| Light source | Compact fluorescent: |
| | - 1 x Genie / E27 / 5-18 W |
| | - 1 x Tornado / E27 / 5-15 W |
| | - 1 x Essential / E27 / 8-18 W |

| | |
|---------------------------|---------------------------------------|
| Lamp included | No |
| Lamp position | Vertical |
| Light distribution | Direct |
| Optic | Prismatic reflector, medium beam |
| Material | Housing: anodized aluminum |
| | Optic: spun aluminum |
| Color | White |
| Installation | Fixation by means of spring fasteners |
| Maintenance | Direct lamp access |

Versions



FBS115 MAX18W

