



Smart CFL-I downlight FBS111/112/113/115/116 – a reliable way to create outstanding lighting

Theta FBS110

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

Benefits

- Safe
- Durable
- Flexible

Features

- Specular diamond faceted reflector for a wide and efficient beam
- Special sandblasted louver for glare-free visual comfort
- New class I three-way connector and sleeving to prevent electrical shocks
- New self-adjusting mounting clips for easy installation
- Suitable for wide range of retrofit energy saving lamps - 3W to 23W CFLs (may vary for different type of luminaires)
- CCC-certified; truly safe and reliable
- Available in five sizes for different cut-outs; two models can be adjusted to accommodate more types of lamp
- Elegant design; integrates perfectly into shop and hotel environments

Theta FBS110

Application

- Households
- Condominiums
- Shops
- Hotels
- Restaurants
- Offices
- Hospitals
- Shopping areas
- Office lobbies
- Hotels, restaurants, hospitals and other public areas

Specifications

Type	FBS111 (cut out Ø 125 mm version)
	FBS112 (cut out Ø 70 mm version)
	FBS113 (cut out Ø 105 mm version)
	FBS115 (cut out Ø 160 mm version)
	FBS116 (cut out Ø 175 mm version)
Light source	Compact fluorescent:
	- 1 x Genie / E27 / 5-18 W
	- 1 x Tornado / E27 / 5-15 W
	- 1 x Essential / E27 / 8-18 W

Lamp included	No
Lamp position	Vertical
Light distribution	Direct
Optic	Prismatic reflector, medium beam
Material	Housing: anodized aluminum
	Optic: spun aluminum
Color	White
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access

Versions



Theta FBS113 downlight



Theta FBS110 downlight

Approval and Application

Ingress protection code IP20

General Information

Cap-Base E27

Protection class IEC Safety class II (II)

Kombipack -

Number of light sources 1

Mechanical and Housing

Colour White

Operating and Electrical

Theta FBS110

Order Code	Full Product Name	Input Voltage	Maximum lamp power
910403630460	FBS113 MAX15W-E27 220V	220 V	MAX15
911401141480	FBS110 C MAX18W-E27 220-240V TH	220 to 240 V	MAX18

General Information

Order Code	Full Product Name	Country version	Lamp family Gear code	Lamp power
910403630460	FBS113 MAX15W-E27 220V	NO	- -	-

Order Code	Full Product Name	Country version	Lamp family Gear code	Lamp power
911401141480	FBS110 C MAX18W-E27 220-240V TH	TH	- ESSENTIAL	18 W

