



Smart CFL-I downlight FBS111/112/113/115/116 – a reliable way to create outstanding lighting

Theta FBS110

Our Smart CFL-I downlight is a safe, reliable and flexible solution that comes in five sizes for different cut-outs. Its elegant design guarantees a perfect fit in any retail or hospitality environment. And because the downlight has been designed specifically for CFL-I lamps, installation and maintenance couldn't be any simpler.

Benefits

- \cdot Safe
- Durable
- Flexible

Features

- \cdot Specular diamond faceted reflector for a wide and efficient beam
- Special sandblasted louver for glare-free visual comfort
- \cdot New class I three-way connector and sleeving to prevent electrical shocks
- \cdot New self-adjusting mounting clips for easy installation
- Suitable for wide range of retrofit energy saving lamps 3W to 23W CFLs (may varies for different type of luminaires)
- CCC-certified; truly safe and reliable
- Available in five sizes for different cut-outs; two models can be adjusted to accommodate more types of lamp
- · Elegant design; integrates perfectly into shop and hotel environments

Theta FBS110

Application

- Households
- \cdot Condominiums
- Shops
- Hotels
- \cdot Restaurants
- Offices
- \cdot Hospitals
- \cdot Shopping areas
- \cdot Office lobbies
- $\boldsymbol{\cdot}$ Hotels, restaurants, hospitals and other public areas

Specifications

FBS111 (cut out Ø 125 mm version)	Lamp included	No	
EB6112 (+ @ 70			
FBS112 (cut out Ø 70 mm version)	Lamp position	Vertical	
FBS113 (cut out Ø 105 mm version)	Light distribution	Direct	
FBS115 (cut out Ø 160 mm version)	Optic	Prismatic reflector, medium beam	
FBS116 (cut out Ø 175 mm version)	Material	Housing: anodized aluminum	
Compact fluorescent:		Optic: spinned aluminum	
- 1 x Genie / E27 / 5-18 W - 1 x Tornado / E27 / 5-15 W	Color	White	
	Installation	Fixation by means of spring fasteners	
- 1 x Essential / E27 / 8-18 W	Maintenance	Direct lamp access	
	FBS115 (cut out Ø 160 mm version) FBS116 (cut out Ø 175 mm version) Compact fluorescent: - 1 x Genie / E27 / 5-18 W - 1 x Tornado / E27 / 5-15 W	FBS115 (cut out Ø 160 mm version) Optic FBS116 (cut out Ø 175 mm version) Material Compact fluorescent: - - 1 x Genie / E27 / 5-18 W Color - 1 x Tornado / E27 / 5-15 W Installation	FBS115 (cut out Ø 160 mm version) Optic Prismatic reflector, medium beam FBS115 (cut out Ø 175 mm version) Material Housing: anodized aluminum Compact fluorescent: Optic: spinned aluminum -1 x Genie / E27 / 5-18 W Color White -1 x Tornado / E27 / 5-15 W Installation Fixation by means of spring fasteners

Versions



FBS110 C MAX18W



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.