



Europa 2 – efficient and easy

Europa 2

Europa 2 is a fixed recessed downlight for compact fluorescent PL-C lamps with highly efficient optics and automatic fixing clips for quick and easy installation. These downlights are available in two formats and can be fitted with a prismatic light control panel, opal cover, clear front panel or glare-control louver. Europa 2 is available in a ready-to-install kit version.

Οφέλη

- No hassle – ready-to-install kit with a flexible gear connection, thereby saving on installation time
- 'Green' promise – high-frequency gear, energy-saving PL-C lamps and less material used in production and packaging
- Modern rim design and pendant glass accessories

Χαρακτηριστικά

- 1- and 2-CFL lamp versions and different lamp colors
- Emergency lighting: 1- and 3-hour versions available
- Cover accessories and decorative pendant glasses
- Highly efficient aluminum-covered reflector (aluminum layer is damped on)
- Tilttable lamp holders ensure easy lamp replacement
- Flexible connection between gear and luminaire

Εφαρμογή

- Offices – corridors, entrances, toilet areas
- Retail – general lighting

Σχεδιάγραμμα διαστάσεων

Europa 2 FBS120

