



F/MBS145

FBH/FBS145 C

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Features

- Modular concept - same cut out diameter allows a consistent appearance and interchangeable accessories and components
- Adjustable swing out metal clip integrates easily into various ceiling systems
- Maintenance is simplified with direct lamp access from below
- Employs highly efficient reflector with a polished upper part to increase reflection while the frosted lower part contributes to better glare control
- Die cast aluminium housing creates a compact and sturdy architecture to interface with different accessories

Application

- Mixed use shopping centres
- Corridors
- Department stores - general lighting
- High-end fashion shops and boutiques
- Restaurants, cafeterias and hotels
- Museum display, public buildings and waiting areas
- Transport buildings e.g. airport terminals and interchanges
- Small offices and conference rooms

FBH/FBS145 C

Versions



Approval and Application

Ingress protection code	IP20
-------------------------	------

General Information

Country version	NO
-----------------	----

Mechanical and Housing

Colour	White
--------	-------

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Maximum lamp power
03630222	FBH145 C 1xPL-C/4P18W HFP WH	220 V	-
03630225	FBH145 C 1xPL-C/4P26W HFP WH	220 V	-
03630232	FBH145 C 2xPL-C/4P18W HFP WH	220 V	-
03630236	FBH145 C 2xPL-C/4P26W HFP WH	220 V	-
00829480	MBS145 C 1xCDM-TD70W IC WH	-	No

Order Code	Full Product Name	Input Voltage	Maximum lamp power
00829580	MBS145 C 1xCDM-TD150W IC WH	-	No
00829680	MBS145 C 1xCDM-T70W IC WH	-	No
00829780	MBS145 C 1xCDM-T150W IC WH	-	No
00830280	FBS145 C 1xPL-C/2P18W IC FG WH	-	No
00830480	MBS145 C 1xCDM-T35W IC WH	-	No

General Information

Order Code	Full Product Name	Cap-Base	Compensation circuit	Optical cover/lens type	Gear	Lamp family code	Lamp power	Number of light sources
03630222	FBH145 C 1xPL-C/4P18W HFP WH	-	-	No	EBP	PL-C/4P	18 W	1
03630225	FBH145 C 1xPL-C/4P26W HFP WH	-	-	No	EBP	PL-C/4P	26 W	1
03630232	FBH145 C 2xPL-C/4P18W HFP WH	-	-	No	EBP	PL-C/4P	18 W	2
03630236	FBH145 C 2xPL-C/4P26W HFP WH	-	-	No	EBP	PL-C/4P	26 W	2
00829480	MBS145 C 1xCDM-TD70W IC WH	-	Inductive parallel compensated	No	CONV	CDM-TD	70 W	1
00829580	MBS145 C 1xCDM-TD150W IC WH	-	Inductive parallel compensated	No	CONV	CDM-TD	150 W	1
00829680	MBS145 C 1xCDM-T70W IC WH	-	Inductive parallel compensated	No	CONV	CDM-T	70 W	1
00829780	MBS145 C 1xCDM-T150W IC WH	-	Inductive parallel compensated	No	CONV	CDM-T	150 W	1
00830280	FBS145 C 1xPL-C/2P18W IC FG WH	-	Inductive parallel compensated	FG	CONV	PL-C/2P	18 W	1
00830480	MBS145 C 1xCDM-T35W IC WH	-	Inductive parallel compensated	No	CONV	CDM-T	35 W	1

