



F/MBS145

FBH/FBS145 C

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

Features

- Modular concept - same cut out diameter allows a consistent appearance and interchangeable accessories and components
- Adjustable swing out metal clip integrates easily into various ceiling systems
- Maintenance is simplified with direct lamp access from below
- Employs highly efficient reflector with a polished upper part to increase reflection while the frosted lower part contributes to better glare control
- Die cast aluminium housing creates a compact and sturdy architecture to interface with different accessories

Application

- Mixed use shopping centres
- Corridors
- Department stores - general lighting
- High-end fashion shops and boutiques
- Restaurants, cafeterias and hotels
- Museum display, public buildings and waiting areas
- Transport buildings e.g. airport terminals and interchanges
- Small offices and conference rooms

FBH/FBS145 C

Versions



Approval and Application

Ingress protection code IP20

Mechanical and Housing

Colour White

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Maximum lamp power	Order Code	Full Product Name	Input Voltage	Maximum lamp power
910403630206	FBH125 1xPL-C/2P10W I WH	-	No	910403630226	FBH145 C 2xPL-C/2P13W IC WH	220 V	-
910403630207	FBH125 1xPL-C/2P13W I WH	-	No	910403630228	FBH145 C 2xPL-C/4P13W HFP WH	220 V	-
910403630208	FBH125 C 1xPL-C/4P13W EBC WH	-	No	910403630229	FBH145 C 2xPL-C/2P18W I WH	220 V	-
910403630209	FBH125 C 1xPL-C/4P13W HFP WH	-	No	910403630230	FBH145 C 2xPL-C/2P18W IC WH	220 V	-
910403630210	FBH135 C 1xPL-C/2P13W I WH	-	No	910403630232	FBH145 C 2xPL-C/4P18W HFP WH	220 V	-
910403630211	FBH135 C 1xPL-C/4P13W EBC WH	-	No	910403630233	FBH145 C 2xPL-C/2P26W I WH	220 V	-
910403630213	FBH135 C 1xPL-C/2P18W I WH	-	No	910403630234	FBH145 C 2xPL-C/4P26W IC WH	220 V	-
910403630214	FBH135 C 1xPL-C/4P18W EBC WH	-	No	910403630236	FBH145 C 2xPL-C/4P26W HFP WH	220 V	-
910403630215	FBH135 C 1xPL-C/4P18W HFP WH	-	No	910403630240	FBH155 C 2xPL-C/4P18W HFP WH	-	No
910403630216	FBH145 C 1xPL-C/2P13W I WH	-	No	910403630244	FBH155 C 2xPL-C/4P26W HFP WH	-	No
910403630218	FBH145 C 1xPL-C/2P26W I WH	-	No	911400829180	FBS145 C 1xPL-C/2P13W I WH	-	No
910403630219	FBH145 C 2xPL-C/2P13W I WH	-	No	911400829280	FBS145 C 1xPL-C/2P18W I WH	-	No
910403630220	FBH145 C 1xPL-C/2P18W IC WH	220 V	-	911400829380	FBS145 C 1xPL-C/2P13W I FG WH	-	No
910403630222	FBH145 C 1xPL-C/4P18W HFP WH	220 V	-	911400829480	MBS145 C 1xCDM-TD70W IC WH	-	No
910403630223	FBH145 C 1xPL-C/2P26W IC WH	220 V	-	911400829780	MBS145 C 1xCDM-T150W IC WH	-	No
910403630225	FBH145 C 1xPL-C/4P26W HFP WH	220 V	-	911400829980	FBS145 C 1xPL-C/2P26W I WH	-	No

General Information (1/2)

Order Code	Full Product Name	Cap-Base	Compensation circuit	Country version	Optical cover/lens type	Gear	Lamp family code	Lamp power
910403630206	FBH125 1xPL-C/2P10W I WH	-	Inductive	NO	No	-	PL-C/2P	10 W
910403630207	FBH125 1xPL-C/2P13W I WH	-	Inductive	NO	No	-	PL-C/2P	13 W
910403630208	FBH125 C 1xPL-C/4P13W EBC WH	-	-	NO	No	EBE	PL-C/4P	13 W
910403630209	FBH125 C 1xPL-C/4P13W HFP WH	-	-	NO	No	EBP	PL-C/4P	13 W
910403630210	FBH135 C 1xPL-C/2P13W I WH	-	Inductive	NO	No	CONV	PL-C/2P	13 W
910403630211	FBH135 C 1xPL-C/4P13W EBC WH	-	-	NO	No	EBE	PL-C/4P	13 W
910403630213	FBH135 C 1xPL-C/2P18W I WH	-	Inductive	NO	No	CONV	PL-C/2P	18 W
910403630214	FBH135 C 1xPL-C/4P18W EBC WH	-	-	NO	No	EBE	PL-C/4P	18 W
910403630215	FBH135 C 1xPL-C/4P18W HFP WH	-	-	NO	No	EBP	PL-C/4P	18 W

FBH/FBS145 C

Order Code	Full Product Name	Cap-Base	Compensation circuit	Country version	Optical cover/lens type	Gear	Lamp family code	Lamp power
910403630216	FBH145 C 1xPL-C/2P13W I WH	-	Inductive	NO	No	CONV	PL-C/2P	13 W
910403630218	FBH145 C 1xPL-C/2P26W I WH	-	Inductive	NO	No	CONV	PL-C/2P	26 W
910403630219	FBH145 C 2xPL-C/2P13W I WH	-	Inductive	NO	No	CONV	PL-C/2P	13 W
910403630220	FBH145 C 1xPL-C/2P18W IC WH	-	Inductive parallel compensated	-	-	CONV	PL-C/2P	18 W
910403630222	FBH145 C 1xPL-C/4P18W HFP WH	-	-	NO	No	EBP	PL-C/4P	18 W
910403630223	FBH145 C 1xPL-C/2P26W IC WH	-	Inductive parallel compensated	NO	No	CONV	PL-C/2P	26 W
910403630225	FBH145 C 1xPL-C/4P26W HFP WH	-	-	NO	No	EBP	PL-C/4P	26 W
910403630226	FBH145 C 2xPL-C/2P13W IC WH	-	Inductive parallel compensated	NO	No	CONV	PL-C/2P	13 W
910403630228	FBH145 C 2xPL-C/4P13W HFP WH	-	-	NO	No	EBP	PL-C/4P	13 W
910403630229	FBH145 C 2xPL-C/2P18W I WH	-	Inductive	NO	No	CONV	PL-C/2P	18 W
910403630230	FBH145 C 2xPL-C/2P18W IC WH	-	Inductive parallel compensated	NO	No	CONV	PL-C/2P	18 W
910403630232	FBH145 C 2xPL-C/4P18W HFP WH	-	-	NO	No	EBP	PL-C/4P	18 W
910403630233	FBH145 C 2xPL-C/2P26W I WH	-	Inductive	NO	No	CONV	PL-C/2P	26 W
910403630234	FBH145 C 2xPL-C/2P26W IC WH	-	Inductive parallel compensated	NO	No	CONV	PL-C/2P	26 W
910403630236	FBH145 C 2xPL-C/4P26W HFP WH	-	-	NO	No	EBP	PL-C/4P	26 W
910403630240	FBH155 C 2xPL-C/4P18W HFP WH	-	-	NO	No	EBP	PL-C/4P	18 W
910403630244	FBH155 C 2xPL-C/4P26W HFP WH	-	-	NO	No	EBP	PL-C/4P	26 W
911400829180	FBS145 C 1xPL-C/2P13W I WH	-	Inductive	NO	No	CONV	PL-C/2P	13 W
911400829280	FBS145 C 1xPL-C/2P18W I WH	-	Inductive	NO	No	CONV	PL-C/2P	18 W
911400829380	FBS145 C 1xPL-C/2P13W I FG WH	-	Inductive	NO	FG	CONV	PL-C/2P	13 W
911400829480	MBS145 C 1xCDM-TD70W IC WH	-	Inductive parallel compensated	NO	No	CONV	CDM-TD	70 W
911400829780	MBS145 C 1xCDM-T150W IC WH	-	Inductive parallel compensated	NO	No	CONV	CDM-T	150 W
911400829980	FBS145 C 1xPL-C/2P26W I WH	-	Inductive	NO	No	CONV	PL-C/2P	26 W

General Information (2/2)

Order Code	Full Product Name	Number of light sources	Order Code	Full Product Name	Number of light sources
910403630206	FBH125 1xPL-C/2P10W I WH	1	910403630226	FBH145 C 2xPL-C/2P13W IC WH	2
910403630207	FBH125 1xPL-C/2P13W I WH	1	910403630228	FBH145 C 2xPL-C/4P13W HFP WH	2
910403630208	FBH125 C 1xPL-C/4P13W EBC WH	1	910403630229	FBH145 C 2xPL-C/2P18W I WH	2
910403630209	FBH125 C 1xPL-C/4P13W HFP WH	1	910403630230	FBH145 C 2xPL-C/2P18W IC WH	2
910403630210	FBH135 C 1xPL-C/2P13W I WH	1	910403630232	FBH145 C 2xPL-C/4P18W HFP WH	2
910403630211	FBH135 C 1xPL-C/4P13W EBC WH	1	910403630233	FBH145 C 2xPL-C/2P26W I WH	2
910403630213	FBH135 C 1xPL-C/2P18W I WH	1	910403630234	FBH145 C 2xPL-C/2P26W IC WH	2
910403630214	FBH135 C 1xPL-C/4P18W EBC WH	1	910403630236	FBH145 C 2xPL-C/4P26W HFP WH	2
910403630215	FBH135 C 1xPL-C/4P18W HFP WH	1	910403630240	FBH155 C 2xPL-C/4P18W HFP WH	2
910403630216	FBH145 C 1xPL-C/2P13W I WH	1	910403630244	FBH155 C 2xPL-C/4P26W HFP WH	2
910403630218	FBH145 C 1xPL-C/2P26W I WH	1	911400829180	FBS145 C 1xPL-C/2P13W I WH	1
910403630219	FBH145 C 2xPL-C/2P13W I WH	2	911400829280	FBS145 C 1xPL-C/2P18W I WH	1
910403630220	FBH145 C 1xPL-C/2P18W IC WH	1	911400829380	FBS145 C 1xPL-C/2P13W I FG WH	1
910403630222	FBH145 C 1xPL-C/4P18W HFP WH	1	911400829480	MBS145 C 1xCDM-TD70W IC WH	1
910403630223	FBH145 C 1xPL-C/2P26W IC WH	1	911400829780	MBS145 C 1xCDM-T150W IC WH	1
910403630225	FBH145 C 1xPL-C/4P26W HFP WH	1	911400829980	FBS145 C 1xPL-C/2P26W I WH	1

