



# F/MBS145

## FBH/FBS145 C

Professional standard recessed downlights with a 145mm internal diameter. Complete with a very efficient highly polished reflector in silver aluminium finish. Suitable for incandescent, halogen, compact fluorescent and high intensity discharge lamps.

### Features

- Modular concept - same cut out diameter allows a consistent appearance and interchangeable accessories and components
- Adjustable swing out metal clip integrates easily into various ceiling systems
- Maintenance is simplified with direct lamp access from below
- Employs highly efficient reflector with a polished upper part to increase reflection while the frosted lower part contributes to better glare control
- Die cast aluminium housing creates a compact and sturdy architecture to interface with different accessories

### Application

- Mixed use shopping centres
- Corridors
- Department stores - general lighting
- High-end fashion shops and boutiques
- Restaurants, cafeterias and hotels
- Museum display, public buildings and waiting areas
- Transport buildings e.g. airport terminals and interchanges
- Small offices and conference rooms

# FBH/FBS145 C

## Versions



### Approval and Application

Ingress protection code IP20

### General Information

Country version NO

Gear CONV

### Mechanical and Housing

Colour White

## Operating and Electrical

Order Code	Full Product Name	Input Voltage	Maximum lamp power	Order Code	Full Product Name	Input Voltage	Maximum lamp power
910403630229	FBH145 C 2xPL-C/2P18W I WH	220 V	-	911400829580	MBS145 C 1xCDM-TD150W IC WH	-	No
910403630233	FBH145 C 2xPL-C/2P26W I WH	220 V	-	911400829680	MBS145 C 1xCDM-T70W IC WH	-	No
911400829380	FBS145 C 1xPL-C/2P13W I FG WH	-	No	911400829780	MBS145 C 1xCDM-T150W IC WH	-	No
911400829480	MBS145 C 1xCDM-TD70W IC WH	-	No	911400830480	MBS145 C 1xCDM-T35W IC WH	-	No

## General Information

Order Code	Full Product Name	Cap-Base	Compensation circuit	Optical cover/lens type	Lamp family code	Lamp power	Number of light sources
910403630229	FBH145 C 2xPL-C/2P18W I WH	-	Inductive	No	PL-C/2P	18 W	2
910403630233	FBH145 C 2xPL-C/2P26W I WH	-	Inductive	No	PL-C/2P	26 W	2
911400829380	FBS145 C 1xPL-C/2P13W I FG WH	-	Inductive	FG	PL-C/2P	13 W	1
911400829480	MBS145 C 1xCDM-TD70W IC WH	-	Inductive parallel compensated	No	CDM-TD	70 W	1
911400829580	MBS145 C 1xCDM-TD150W IC WH	-	Inductive parallel compensated	No	CDM-TD	150 W	1
911400829680	MBS145 C 1xCDM-T70W IC WH	-	Inductive parallel compensated	No	CDM-T	70 W	1
911400829780	MBS145 C 1xCDM-T150W IC WH	-	Inductive parallel compensated	No	CDM-T	150 W	1
911400830480	MBS145 C 1xCDM-T35W IC WH	-	Inductive parallel compensated	No	CDM-T	35 W	1

