



High light output and attractive design

Europa

The Europa range offers high performance and an attractive design. It offers an effective solution for various types of commercial establishments since it optimizes the use of electrical energy whilst also ensuring visual comfort. The downlighters of the Europa range create a pleasant and inviting atmosphere, making the lighting an excellent way to promote sales.

Benefits

- Easy to install
- High performance
- Excellent finish on entire luminaire
- Easy access to lamps with the Easy Open system, easy maintenance

Features

- Torino model - Tempered and frosted glass, die-cast aluminum rim in white color, anodized aluminum reflector and stainless-steel fixing springs
- Milano model - Tempered and screen-printed glass, die-cast aluminum rim in white color, anodized aluminum reflector and stainless-steel fixing springs
- Firenze model - Transparent and screen-printed tempered glass, die-cast aluminum rim in white, anodized aluminum reflector and stainless-steel fixing springs

Application

- Ideal for general lighting in shopping centers, shops, hotels and offices

Specifications

Type	FBS672	Light source	2 x 18 W, 2 x 26 W / PL-C 2P
	FBS675		2 x 18 W, 2 x 26 W / PL-C 4P

Mains voltage	Electromagnetic (high power factor): 220 V - 60 Hz
	Electronic 220 V / 60-50 Hz: (EB)
Optical cover	Tempered and frosted glass (FBS672)
	Tempered and screen-printed glass (FBS675)

Specifications

Type	MBS675
Light source	1 x 70 W, 1x150 W / MHN-TD
	1 x 70 W, 1x150 W / CDM-TD
Mains voltage	Electromagnetic (high power factor): 220 V / 60 Hz
	Independent: electronic 220 V / 60-50 Hz

Materials and finishing	Die-cast aluminum rim in white color, anodized aluminum reflector and stainless-steel fixing springs
Installation	Recessed in the ceiling, in niches of Ø 200 mm

Optical cover	Tempered and screen-printed glass
Materials and finishing	Die-cast aluminum rim in white color, anodized aluminum reflector and stainless steel fixing springs
Installation	Recessed in the ceiling, in niches of Ø 200 mm

Versions



Operating and Electrical

Input Voltage	220 V
----------------------	-------

Mechanical and Housing

Color	White
--------------	-------

General Information

Order Code	Full Product Name	Optical cover/lens type	Gear	Kombipack	Lamp family code	Lamp power	Number of light sources
919106027453	FBS672 2xPL-C/4P18W/840 EB GF WH	Glass frosted	EB	-	PL-C/4P	18 W	2 pcs
919106031101	FBS672 2XPL-C/4P26W/840 EB GF WH	Glass frosted	EB	-	PL-C/4P	26 W	2 pcs
919306012601	FBS672 2XPL-C/2P18W/840 220V-60Hz GF WH	Glass frosted	-	-	PL-C/2P	18 W	2 pcs
919306012611	FBS672 2XPL-C/2P26W/840 220V-60Hz GF WH	Glass frosted	-	-	PL-C/2P	26 W	2 pcs
919106027488	FBS675 2xPL-C/4P26W/840 EB DG WH	Decorative glass	EB	-	PL-C/4P	26 W	2 pcs
919106031099	FBS675 2xPL-C/4P18W/840 EB DG WH	Decorative glass	EB	-	PL-C/4P	18 W	2 pcs
919306012628	FBS675 2xPL-C/2P18W/840 220V-60HZ DG WH	-	-	Lamp(s) included	PL-C/2P	18 W	2 pcs
919306012637	FBS675 2xPL-C/2P26W/840 220V-60HZ DG WH	-	-	Lamp(s) included	PL-C/2P	26 W	2 pcs
919306012561	MBS675 1xMHN-TD70W/842 DG WH	Decorative glass	-	-	MHN-TD	70 W	1 pc
919306012571	MBS675 1xMHN-TD150W/842 DG WH	Decorative glass	-	-	MHN-TD	150 W	1 pc
919306012581	MBS675 1XCDM-TD70W/830 EB DG WH	Decorative glass	-	-	CDM-TD	70 W	1 pc
919306012591	MBS675 1XCDM-TD150W/830 EB DG WH	Decorative glass	-	-	CDM-TD	150 W	1 pc

