



FCC110/120 and FWC110/120/121 – all- night security

FCC110/120 XCC120

FCC110/120 and XCC120 (ceiling-mounted) are attractive, low-energy luminaires for all-night security and amenity lighting. The high-reflectance white plate and translucent bowl with prismatic control produce excellent light distribution for low-level lighting of walls, corridors and surroundings.

Benefits

- Low-energy luminaires for economical all-night security and amenity lighting
- Excellent light control for low-level lighting of walls, corridors and surroundings, thanks to high optical performance of mirror and refractor bowl
- Choice of long-life lamps for low maintenance costs

Features

- Choice of long-life lamps
- Low energy consumption
- Mirror and refractor bowl

Application

- Residential areas
- Industry
- Security lighting

Specifications

Type	FCC110	Light source	FCC110
	FCC/XCC120		Compact fluorescent: - 1 x MASTER PL-S 2 Pin / G23 / 9 W

FCC110/120 XCC120

	FCC120
	Compact fluorescent:
	- 1 x MASTER PL-C 2 Pin / G24d-2 / 18 W
	XCC120
	HID:
	- 1 x MASTER SOX-E / BY22d / 18 W
Lamp included	Yes (K or lamp color 827)
Mains voltage	230 or 240 V
Option	Photocell integrated (PH)

Materials	Housing: injection-moulded ASA, non-corrosive
	Bowl: polycarbonate, translucent
	Unit plate: polycarbonate
Color	Housing and unit plate: white
Installation	Wall ceiling mounting
	Cable entries on all sides allow through-wiring
Remarks	Luminaires are ready-to-install versions; lamp and installation material included

Versions

