



Compact and robust design

D'ECO Light Collection FCS321

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Benefits

- Easy to install
- Wide variety of optical systems
- Fine frame
- High performance

Features

- Aluminum-plate body in white color
- Aluminum reflector with metallic finish
- Round or square frame
- Recessed or surface-mounted
- Options with flat frosted glass, recessed frosted glass or recessed glass with 4 or 9-wing shade
- For the MHN / CDM-TD metal-halide lamp version there is also a chassis with equipment (ballast)

Application

- Ideal for general lighting in shops, hotels and offices

Specifications

Type	FCS321	Light source	2 x 18 W, 2 x 26 W / PL-C 4P
------	--------	--------------	------------------------------

D'ECO Light Collection FCS321

	2 x 32 W / PL-T 4P
Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
Optical cover	Frosted recessed glass

Materials and finishing	Aluminum-plate body and aluminum reflector with metallic finish
Installation	Surface-mounted on the ceiling

Versions



Operating and Electrical

Input Voltage	220 V
----------------------	-------

General Information

Optical cover/lens type	Glass frosted
Gear	EB
Number of light sources	2 pcs

Mechanical and Housing

Color	White
--------------	-------

General Information

Order Code	Full Product Name	Lamp family code	Lamp power
919406004971	FCS321 2XPL-C/4P18W/840 EB GF WH	PL-C/4P	18 W
919406004981	FCS321 2XPL-C/4P26W/840 EB GF WH	PL-C/4P	26 W

Order Code	Full Product Name	Lamp family code	Lamp power
919406004991	FCS321 2XPL-T/4P32W/840 EB GF WH	PL-T/4P	32 W

