



Flexible system design and brilliant optical control

FastFlex LED module

Philips FastFlex LED module offers high-quality, reliable, easy-to-use outdoor LED illumination for roads and urban street lighting. The system offers outstanding optical control and flexible system design.

Advantages

- Perfectly match each project's needs
- Easy factory assembly and reliable lifetime performance
- Low cost of thermal management

Fonctions

- Modular approach to luminaire design; choice of 4 optical distributions
- LUXEON T LEDs in CCT 4000 K, CRI 70 or 80
- Patented interface between lens, module and mounting surface
- High Tcase 75 °C
- Lean supply chain

Application

- Road lighting
- Flood and Area lighting
- Urban street lighting

FastFlex LED module

Versions







Schéma dimensionnel



Product
FastFlex lens 2x8/V




Product
FastFlex lens 2x8/IV-X



Product
FastFlex lens 2x8/III-X

FastFlex LED module

Schéma dimensionnel



Product

FastFlex lens 2x8/II-X

