



Product Description

PAR38

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Οφέλη

- Produces the same useful light as conventional PAR lamps at 20% lower energy

Χαρακτηριστικά

- Spot versions have a stippled front reflector producing a narrow, homogeneous beam
- Flood versions have a front refractor composed of prismatic elements

Εφαρμογή


- Can be used indoors and outdoors, or wherever blown-bulb reflector lamps would be too vulnerable
- Indoors: shops, window displays, homes, hotels, restaurants, theatres, museums, exhibitions and buildings
- Outdoors: floodlighting, advertising signs, buildings, statues, podiums, sports grounds, parks and gardens
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder

PAR38

Versions




Σχεδιάγραμμα διαστάσεων




Product	D (max)	C (max)	C1
PAR38 120W E27 24V SP 10D 1CT/12	123 mm	137 mm	123 mm

Light Distribution Diagrams



Accent Diagrams



Beam Diagrams

