



# Put people and merchandise in the best light

## PAR20

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

### Benefits

- Reduced maintenance and operating costs.
- Create a variety of atmospheres and provide a comfortable shopping experience.
- Variety of beam spreads and wattages

### Features

- Beam spreads ranging from spot to flood.
- Philips Halogen lamps last 2000–4000 hours rated average life†.
- Bright, White Light.
- Optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering.
- Available in 50 Watts Spot and Flood 120 and 130 volts.
- † Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not..

### Application

- Ideal for retail, residential, and commercial applications. For indoor and outdoor use.


# PAR20

## Versions



E26, PAR20, Flood

## Dimensional drawing



### Product

39PAR20/EVP/FL25 120V 15/1

