



Put people and merchandise in the best light

Long Life IR PAR30S

Optically advanced Halogen PAR lamps are designed with innovative technologies that provide superior light performance while reducing operating costs.

Benefits

- Delivers consistent quality lamp-to-lamp and throughout lifetime.
- Increased uniform beam intensity without hot spots.
- Superior beam control for effective accent lighting.

Features

- Philips reflector technology provide optimal beam control and uniform beam intensity without hot spots.
- Features IRC coating technology.
- 6000 Hour Rated Average Life †
- Available in 45 Watts Spot, Flood, Wide Flood.
- †This excludes the 130V 50W PAR30 Short which has 3000 hours. Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not

Application

- Ideal for retail, residential, and commercial applications. For indoor and outdoor use.


Long Life IR PAR30S

Versions



E26, PAR30/PAR30S, Wide Flood, Med

Dimensional drawing



Product	D	C (max)
Long Life IR 50PAR30L/IRC+/WFL40 120V 15/1	3.75 in	4.5 in

