



Product Description

Accentline

Low-voltage halogen burner optically positioned in a glass reflector with and without front glass

Benefits

- Good light quality, cool beam halogen light and a professional lifetime

Features

- Dichroic reflector coating is heat-transmitting towards the back and light-reflecting towards the front of the lamp
- UV-Block burner
- Excellent colour rendering
- GU5.3 base for extra retention in luminaire


Application

- Accent, task lighting and decorative applications in homes, shops, hotels and restaurants

Versions



Dimensional drawing



Product	D (max)	C (max)
Accent 35W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm
Accent 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

General Information	
Cap-Base	GU5.3
Rated Lifetime (Hours)	4,000 hour(s)
Switching Cycle	16,000
Nominal lifetime	4,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	Instant full light s
Voltage (Nom)	12 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16

Light Technical

Order Code	Full Product Name	Luminous Flux
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	430 lm
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	680 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/10X5F	35 W

Order Code	Full Product Name	Power Consumption
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	50 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
58842000	Accentline 35W 4000h GU5.3 12V 36D 1CT/ 10X5F	37 kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
58845100	Accentline 50W 4000h GU5.3 12V 36D 1CT/ 10X5F	53 kWh

