



ET-Standard Transformer

ET-S transformer

High-frequency electronic transformer (60, 105 and 150 W versions available), operation with 12 V halogen lamps

Benefits

- High efficiency compared with magnetic transformer
- Easy luminaire design-in with EMI compliance
- Dimmable with Philips-approved leading- and trailing-edge dimmers

Features

- 30,000 hours lifetime
- EMI-compliant
- Screw connector
- CE, SELV approval
- Safe operation with overload, short circuit and overheating protection

Application

- Indoor residential: living rooms, decorative and accent lighting
- Professional applications: reception areas, offices, retail spaces and exhibition rooms


ET-S transformer

Versions



ET-S 105

Dimensional drawing



Product	D1	C1	A1	B1
ET-S 105	4.2 mm	33.5 mm	112.0 mm	54.0 mm

