



# Product Description

## HalogenA PAR30S

Mains-voltage 97 mm diameter reflector lamp

### Benefits

- Bright, sparkling halogen light
- Convenient halogen solutions that fit in standard, existing luminaires

### Features

- Hard-glass halogen burner (linear filament) optically positioned in a parabolic, aluminium-coated pressed-glass reflector (PAR)
- Natural colour rendering
- Sparkling, crisp white halogen light
- Good luminous efficacy
- Long life (two to two and a half times the lifetime of a normal incandescent lamp)
- Spot versions have slightly stippled front glass to emphasise the sparkling reflector
- Flood versions have a faceted front glass to prevent glare and ensure a homogeneous beam distribution
- Front glass protects the lamp for safety and prevents touching and dust deposits

### Application

- Typically used for accent and display lighting in shops, especially for premium goods
- Also used as general lighting in hotels, theaters and lobby areas

# HalogenA PAR30S


## Versions




## Dimensional drawing

D

Product	D (max)	C (max)
HalogenA Par30s 75W E27 230V 25D 1CT/15	96 mm	99 mm




## Accent Diagrams



LDAC\_HPAR30S\_75W\_30D-Accent diagram

# HalogenA PAR30S

## Beam Diagrams



LDBE\_HPAR30S\_75W\_30D-Beam diagram

