



Spot of crisp white light from modern-looking aluminum reflector

Aluline 111

Low-voltage halogen burner in decorative aluminum reflector equipped with antiglare cap. Ideal solution for high-end modern luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Aluminum coating
- Lifetime: 3000 hours
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


Aluline 111

Versions




LPPR HALUACN


Dimensional drawing



Product	D (max)	C (max)	C1 (max)
Alu111 50W 4000h G53 12V 24D 1CT/6	111 mm	67 mm	51 mm




Accent Diagrams



Accent Diagram - Alu111 50W 4000h G53 12V 24D 1CT/6

Aluline 111

Beam Diagrams



Beam diagram - Alu111 50W 4000h G53 12V 24D
1CT/6

