



# Spot of crisp white light from modern-looking aluminum reflector

## MASTERLine 111

Low-voltage halogen burner with very high energy efficiency and long lifetime thanks to IRR coating in decorative aluminum reflector equipped with ceramic anti-glare cap. Ideal solution for high-end modern luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

### Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lowest replacement cost due to extra-long lifetime

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Unique infra-red coated burner technology
- Lifetime: 4000 hours
- Instant start

### Application


- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

# MASTERLine 111


## Versions




## Dimensional drawing



| Product                              | D (max) | C (max) | C1 (max) |
|--------------------------------------|---------|---------|----------|
| MASTERLine 111 30W G53 12V 24D 1CT/6 | 111 mm  | 67 mm   | 51 mm    |




## Accent Diagrams



# MASTERLine 111

## Beam Diagrams



LDBE\_HML111\_30W\_24D-Beam diagram

