



# Spot of bright, white light

## Brilliantline Dichroic

Superior-quality low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

### Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Dichroic coating
- Universal burning position
- Instant start

### Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


# Brilliantline Dichroic

## Versions




LPPR HDICHO GU53 60D


## Dimensional drawing



Product	D (max)	C (max)
Brill 50W GU5.3 12V 60D 1CT/10X5F	51 mm	46 mm



## Accent Diagrams



Accent Diagram - Brill 50W GU5.3 12V 60D 1CT/10X5F

Beam Diagrams

$\frac{1}{2}$ beam diameter	h	E	d(m)
-----------------------------	---	---	------

Beam diagram - Brill 50W GU5.3 12V 60D 1CT/  
10X5F

