



Spot of bright white light

Brilliantline Alu

Superior-quality low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

优点

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours

特点

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Universal burning position
- Lifetime: 4000 hours
- Instant start

应用

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

安全提示


- 由于灯泡会散发热量，因此灯泡与易燃材料或容易干燥或褪色的物体之间需相隔至少 0.5 米。

Brilliantline Alu

Versions



二维绘图



Product
Brilliantline Alu 50W GU5.3 12V MR16 36D 1CT/10X5F
Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F

应用	
能效标签 (EEL)	B
控制调光	
可调光	Yes
运营和电气	
电压 (标称)	12 V
启动时间 (标称)	0.0 s
60% 灯光下的预热时间 (标称)	instant full light
基本信息	
底盖	GU5.3
标称寿命 (标称)	4000 h
操作位置	UNIVERSAL
额定使用寿命 (小时)	4000 h
切换循环	16000X
灯具设计要求	
灯泡温度 (最高)	250 °C
照明科技	
光束角度 (标称)	36 °
相关色温 (标称)	3000 K
显色指数 (标称)	100
标称使用寿命结束时灯的光通维持率 (最低)	80 %
额定光束角度	36 °
机械和壳体	
灯泡外观	透明
灯泡外形	MR16

应用

Order Code	Full Product Name	能耗 kWh/1000 h
924057317101	Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F	37 kWh
924057417101	Brilliantline Alu 50W GU5.3 12V MR16 36D 1CT/10X5F	53 kWh

运营和电气

Order Code	Full Product Name	灯具电流 (标称) 称)	功率 (额定) (标
924057317101	Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F	3.00 A	35.0 W

Order Code	Full Product Name	灯具电流 (标称) 称)	功率 (额定) (标
924057417101	Brilliantline Alu 50W GU5.3 12V MR16 36D 1CT/10X5F	4.25 A	50.0 W

基本信息

Order Code	Full Product Name	飞利浦代码
924057317101	Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F	14716

Order Code	Full Product Name	飞利浦代码
924057417101	Brilliantline Alu 50W GU5.3 12V MR16 36D 1CT/10X5F	14717


照明科技

Order Code	Full Product Name	光通量 (额定) (标称)	发光强度 (最大)
924057317101	Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F	460 lm	1500 cd

Order Code	Full Product Name	光通量 (额定) (标称)	发光强度 (最大)
924057417101	Brilliantline Alu 50W GU5.3 12V MR16 36D 1CT/10X5F	780 lm	2100 cd




Accent Diagrams




LDAC_HALUMR_35W_36D-Accent diagram

Beam Diagrams



LDBE_HALUMR_35W_36D-Beam diagram



LDBE_HALUMR_50W_36D-Beam diagram

