

IRR-coated halogen capsule. Compact shape, crisp white light

MASTERCapsule

Low-voltage halogen capsule with very high energy efficiency and long lifetime thanks to IRR coating. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lowest replacement cost due to extra-long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Unique Philips-patented EcoBoost single-ended burner: 40% higher efficiency than standard products
- Universal burning position
- Instant start

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires


MASTERCapsule

Versions



GY6.35, T11, IR Coated

Dimensional drawing



Product	D (max)	L	C (max)
LV Capsule 30W GY6.35 12V IR 1BS/12	12 mm	30 mm	44 mm

