



Compact shape, crisp white light

Capsuleline 迷你燈管

Low-voltage halogen capsule. Ideal solution for small decorative luminaires. UV-block glass and low-pressure filling allow usage without cover glass. The compact Capsuleline delivers crisp white light over a long lifetime.

优点

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

特点

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Compact size, easy to fit in the luminaire
- Universal burning position
- Instant start

应用


- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires

Capsuleline 迷你燈管

Versions



二维绘图



Product	D (max)	L	C (max)
Capsuleline 50W GY6.35 12V CL 2000h 1CT/10X10F	12 mm	30 mm	44 mm

