



產品說明

HF-Performer III for PL-T/C lamps

環保永續、節能效率、超薄機身，PL-T 與 PL-C 螢光燈管專用高頻電子安定器

优点

- Robust design that meets all relevant international safety and performance standards, in combination with good energy efficiency
- Automatic restart (after voltage dip or lamp exchange) ensures easy operation and hassle-free re-lamping.
- Suitable for DC emergency operation, 186 to 275 V (at -10 °C) and in line with IEC/EN 60598-2-22 luminaire norms

特点

- 50,000-hour lifetime at maximum case temperature, combined with over 60,000 on/off switches on one lamp
- Programmed, flicker-free, pre-heated start (< 2.0 s) which allows the lamp to be switched on and off without reducing useful lamp life
- Active power factor correction to ensure constant light, irrespective of mains-voltage fluctuations
- The unit is protected against excessive mains voltage and incorrect connections.

应用


- 適合強調高省電效率的照明應用
- 配合動作偵測控制系統使用，如飛利浦 Philips OccuPlus
- 辦公大樓、醫院、超市、百貨公司、學校
- 等級 I 戶外照明應用，例如工業場所和停車場

HF-Performer III for PL-T/C lamps

Versions



二维绘图



Product	D1	C1	A1	A2	B1	B2
HF-P 1/218 PL-T/C III 220-240V	4.2 mm	30.0 mm	103.8 mm	93.5 mm	67.8 mm	57.5 mm

