




Ürün tanımı:

HF-Performer TL5 Circular

Kompakt, kare, hafif yüksek frekans elektronik standart balastlar

Faydaları

- 50% longer lamp life than with conventional ballasts
- Up to 25% energy saving at constant luminous flux compared with conventional ballasts
- Constant light independent of mains voltage fluctuations

Özellikler


- Programmed start: flicker-free, warm-start circuit
- Protected against excessive mains voltages
- Automatic stop circuit (safety stop) is activated within 5 seconds in case of lamp failure; ballast resets automatically after lamp replacement

Uygulama


- Kontrol sistemli tesisatlar (örn. hareket algılama)
- Ofis binaları, örn. idari ve yönetim ofisleri ve konferans/toplantı odaları
- Dükkanlar ve perakende merkezleri, örn. moda, butikler ve yerel dükkanlar
- Oteller, moteller ve restoranlar dahil konaklama
- Kamu binaları, örn. bankalar, galeriler ve müzeler
- VDE 0108'e göre 2s'de tekrar ateşlemeli acil durum kitlerine uygun. Yalnızca geçici yedek için sürekli işlem için değil

HF-Performer TL5 Circular

Versions



Boyutlu çizim



Product	D1	C1	A1	A2	B1	B2
HF-P 155 TL5C 220-240V 50/60Hz	4.5 mm	30.0 mm	103.0 mm	93.5 mm	67.0 mm	57.5 mm
HF-P 160 TL5C 220-240V 50/60Hz	4.5 mm	30.0 mm	103.0 mm	93.5 mm	67.0 mm	57.5 mm

Çalıştırma ve Elektrikle İlgili Bilgiler

Giriş Frekansı	50 ila 60 Hz
Giriş Voltajı	220 to 240 V

Genel Bilgiler

MCB'deki Ürün Sayısı (16A Tür B) (Nom)	28
Lamba Sayısı	1 piece/unit
Lamba Türü	TL5C

Mekanik Ayrıntılar ve Muhafaza

Muhafaza	S 103x67x30
----------	-------------

Onay ve Uygulama

Order Code	Full Product Name	Enerji Verimliliği İndeksi
92776730	HF-P 155 TL5C 220-240V 50/60HZ	A3

Order Code	Full Product Name	Enerji Verimliliği İndeksi
92778130	HF-P 160 TL5C 220-240V 50/60HZ	A2

Sistem özellikleri

Order Code	Full Product Name	Nominal Balast Lamba Gücü
92776730	HF-P 155 TL5C 220-240V 50/60HZ	55 W

Order Code	Full Product Name	Nominal Balast Lamba Gücü
92778130	HF-P 160 TL5C 220-240V 50/60HZ	60 W

HF-Performer TL5 Circular

