



## 產品說明

### HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

智慧型高頻電子式調節安定器，外型採平面設計，重量輕巧，採用 DALI (數位可定址照明介面) 或觸控與調光按鈕協定，適用於 TL5 螢光燈管。

#### 优点

- Extremely low stand-by losses, controlled cut-off for dim levels above 80%, hybrid control dimming (current control at 100% and power control at 1%) – combined with MASTER TL5 Eco the most energy-efficient solution
- HF operation improves light quality and lamp lifetime.
- Compliant with European and Asian norms and suitable for emergency lighting systems

#### 特点

- HF-R Intelligent recognizes what type of lamp (T5 HE, HO, ECO, TL-D, PL-L) is connected and drives it accordingly
- Programmed start: flicker-free ignition < 1.0 second and striation-free operation, no stroboscopic effects. Preheating the lamp electrodes enables the lamps to be switched on and off without reducing life
- Smart power ensures constant light, independent of mains fluctuations and dimming from 1 to 100%
- Stop circuit is activated within 5 seconds in the event of lamp failure (safety stop), and ballast resets automatically after lamp replacement
- Programmable for intelligent functionalities via Philips MultiOne: Corridor mode, Emergency DC dim level, Burn-in time

#### 应用


- 辦公室需要的調光功能，具備簡單及安裝方便等特性，或是個人的燈光強度調整，例如使用 ActiLume
- DALI 安裝具使用者操控、運用日光及 / 或動作偵測功能
- 使用遙控控制系統的 DALI 安裝
- 依據 EN 60598-2-22 規範的緊急備份安裝，不包含高風險工作區

# HF-Regulator Intelligent Touch DALI for TL5/TL-D/PL-L lamps

## Versions



## 二维绘图



Product	D1	C1	A1	A2	B1
HF-Ri TD 4 14/24 TL5 E+ 195-240V	4.2 mm	22.0 mm	360.0 mm	350.0 mm	39.0 mm

