



Metro HGC007

Metro HGC007

The Metro streetlight luminaire brings a fresh new light to your residential areas, local roads and industrial estates. Metro's compact yet attractive housing easily blends in with your surroundings while making a significant contribution to a safer and more comfortable environment. It comes available with a choice of SON, HPL, CDM-ET and PL-T lamps for a high light output as well as fully integrated gear and mounting brackets for swift and simple installation and maintenance.

Features

- Compact luminaire body, designed to accept a variety of lamps: SON, HPLN, CDM-ET and PL-T
- Quick and easy lamp replacement by removal of twist-lock bowl
- Maintenance of the control gear and lamp holder is via a single slide-out gear/ lamp holder assembly
- Mounting bracket for easy and flexible installation
- Anti-vibration spring supplied for HID lamp versions

Application

- Residential streets
- Areas requiring good security
- Parks and gardens
- Footpaths and access ways
- Conveyor lighting
- General mining lighting
- Home yard lighting
- Industrial lighting