



# EnduraBay HPK238

## EnduraBay HPK138/238

HPK238's attractive and unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. Its robust, dependable construction along with its ease of installation and maintenance truly make this highbay luminaire a durable, yet appealing solution. EnduraBay LX HPK138 Elegance and efficiency were the themes driving the design of EnduraBay LX. Its attractive yet unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. What's more, it is easy on your budget. EnduraBay LX truly offers you peace of mind in your highbay installation. This robust luminaire makes it an impressive light source, as does its attractive minimalist design. The most striking feature of this high-bay luminaire is its four "shields" on the upper part of the housing, giving any lighting installation a distinctive elegance.

### Features

- HPK238
- Attractive outlook with a tangible product quality
- Good light performance with more options for lamp & optics choices
- Designed for safety and durability
- Easy to install and maintain
- Reliable ingress protection
- Easy to specify
- HPK138
- The grooves divide the skin of the cylinder in four robust looking 'shields' which extend beyond the top and bottom of the gear housing, giving a touch of elegance to the luminaire's unique appearance
- For ease of installation. It is equipped with an external mains entry cable, therefore no access is required into the main body of the fitting saving labor and time
- Re-lamping is simple and does not require the use of any tools or the dismantling of any parts"

# EnduraBay HPK138/238

## Application

- General industry
- Logistic centers and warehouses
- Power plants
- Public areas

## Versions



### Operating and Electrical

Input Voltage	230 V
---------------	-------

### General Information

Cap-Base	E40
Protection class IEC	Safety class I (I)
Compensation circuit	Inductive parallel compensated
Gear	CONV
Lamp family code	HPI-P
Number of light sources	1

### Mechanical and Housing

Colour	Black
--------	-------

### General Information

Order Code	Full Product Name	Lamp power	Lamp system description
911401094480	HPK238 1xHPI-P250W-BU IC 230 50 BK	250 W	Base-Up (BU)
911401094580	HPK238 1xHPI-P400W-BUS IC 230 50 BK	400 W	Base-Up/internal Starter (BUS)

