



# VerseBay HPK518

## VerseBay HPK518

Reliable, effective lighting in the industrial workplace is a crucial factor influencing productivity, safety and staff well-being. The VerseBay high-bay luminaire clearly embodies such lighting requirements. Its solid, quality construction and reliable performance excels even in the toughest working environments. Its specially designed beam regulator allows light distribution to be optimally set for a broad range of work areas using just a single reflector. VerseBay also embodies extraordinary features that dramatically eases installation and maintenance. An external waterproof connector makes installation faster than ever while its tool-less lamp replacement is quick and hassle-free. So whatever your high-bay lighting requirements – industrial areas, logistics centers or public spaces – VerseBay offers a host of innovative features that can add new dimensions to versatility and ease of installation.

### Features

- Ideal for industrial applications with extreme conditions such as high temperatures, dusty and even humid environments
- Owing to its high-quality materials, functional design and the modular construction, VerseBay is also particularly suitable for many large spaces with high ceilings
- An integrated beam regulator allows you to adjust beam spread to accommodate two different light beams with only one reflector
- Tool-less installation and wiring
- Easy to maintain
- Made of top quality materials

### Application

- General industries
- Heavy industries
- Logistic centers
- Power plants
- Steel plants
- Public spaces
- Food processing industries

# VerseBay HPK518

## Versions



Operating and Electrical	
Input Voltage	220 V
General Information	
Protection class IEC	Safety class I (I)
Compensation circuit	Inductive parallel compensated
Gear	CONV
Lamp family code	HPI-P
Number of light sources	1

## General Information

Order Code	Full Product Name	Lamp power	Lamp system description
911401089280	HPK518 1xHPI-P250W-BU IC 220V-50Hz	250 W	Base-Up (BU)

Order Code	Full Product Name	Lamp power	Lamp system description
911401089380	HPK518 1xHPI-P400W-BUS IC 220V-50Hz	400 W	Base-Up/internal Starter (BUS)

