



HPK888 Crestbay

Crestbay HPK888

Reliable, effective lighting in any setting is a crucial factor that promotes the senses, productivity, safety and even architecture. Crestbay™ from Philips is precisely designed with this in mind. This highly versatile luminaire delivers outstanding performance in large spaces and in the toughest of environments while assuring quality lighting across a variety of industrial and commercial applications. Moreover, Crestbay™'s innovative SWING-2-BRIGHT™ technology makes maintenance easy, hassle-free and faster than ever before."

Характеристики

- Suitable with a wide range of Philips lamps types; from highpressure mercury and sodium lamps as to compact discharge lamps
- Three types of reflectors: a small aluminium reflector for 70W-250W lamps, a large aluminium reflector for 250W and 400W lamps, and a prismatic acrylic reflector
- All aluminium reflectors have a gloss mirror inner surface with a choice of narrow, medium or wide light beams. Beams can be selected with an adjustable lamp holder
- Each reflector can be fitted with a glass cover to protect against the ingress of dust and moisture
- High-quality components make Crestbay™ able to withstand high ambient temperature
- Easier, safer and faster re-lamping /maintenance via Philips revolutionary SWING-2-BRIGHT™ technology.

Применение

- General industries
- Wet and dusty environments
- Public buildings such as exhibition halls, airports, museums
- Discount stores, hyper/ supermarkets, do-it-yourself shops
- High-end fashion outlets

Crestbay HPK888

Versions



Соответствие требованиям и область применения

Код защиты от проникновения	IP66
-----------------------------	------

Эксплуатационные и электрические характеристики

Входное напряжение	220 V
--------------------	-------

Общая информация

Цепь компенсации	Inductive parallel compensated
------------------	--------------------------------

Тип оптического плафона/линзы	No
-------------------------------	----

ПРА	CONV
-----	------

Количество источников света	1
-----------------------------	---

Общая информация

Order Code	Full Product Name	Класс защиты по МЭК	Kombrack	Код лампового семейства	Мощность лампы	Тип оптики	Описание ламповой системы
02000180	HPK888 1xHPI-P250W-BU IC R-L WH	-	-	HPI-P	250 W	R-L	Base-Up (BU)
02000280	HPK888 1xHPI-P400W-BUS IC R-L WH	-	-	HPI-P	400 W	R-L	Base-Up/internal Starter (BUS)
02000380	HPK888 1xCDM-T250W IC R-S WH	Класс безопасности I	-	CDM-T	250 W	R-S	-
02000680	HPK888 1xSON400W IC R-L GR	-	-	SON	400 W	R-L	-
02000980	HPK888 1xHPI-P250W-BU IC R-L GR	-	-	HPI-P	250 W	R-L	Base-Up (BU)
02001080	HPK888 1xHPI-P400W-BUS IC R-L GR	-	-	HPI-P	400 W	R-L	Base-Up/internal Starter (BUS)

Механические компоненты и корпус

Order Code	Full Product Name	Цвет	Order Code	Full Product Name	Цвет
02000180	HPK888 1xHPI-P250W-BU IC R-L WH	White	02000680	HPK888 1xSON400W IC R-L GR	Gray
02000280	HPK888 1xHPI-P400W-BUS IC R-L WH	White	02000980	HPK888 1xHPI-P250W-BU IC R-L GR	Gray
02000380	HPK888 1xCDM-T250W IC R-S WH	White	02001080	HPK888 1xHPI-P400W-BUS IC R-L GR	Gray

